

NEW YEAR NEW GEAR 22

FLUKE®

1 DEC 2021 - 28 FEB 2022

Offers valued up to \$637!



The World's first and only CAT III 1500 V DC Clamp Meter.

NEW

Fluke 393 FC CAT III 1500 V True-RMS Clamp Meter with iFlex®

Whether it's solar arrays, wind farms, electric railways or battery banks – the Fluke 393 FC is specially designed for uninterrupted, high voltage DC environments.

- Measure safely with CAT III 1500 V rated clamp meter
- Thin jaw for access to cables in crowded combiner boxes
- Sturdy IP54 rated for outdoor use
- Work efficiently with DC power measurement, audio polarity and visual continuity features



Thinner jaws, thicker cables.

The thin jaws on the Fluke 393 FC are well suited to navigating tight spaces in combiner boxes and inverters, while the 34 mm jaw opening allows you to measure thicker cables with ease.



Fluke Connect® enabled.

Pair your Fluke tools to your mobile device or PC to monitor readings, track measurements and generate reports from anywhere, remotely or in the field with the free Fluke Connect app.



Scan QR code for more info
fluke.co/NYNG22

See offers inside 



Fluke 370 Series AC/DC True-RMS Clamp Meters

Advanced troubleshooting performance.

- Record, analyse and share results with Fluke Connect®
- Non-contact measurement using FieldSense™ technology for increased safety (377 FC & 378 FC)
- Identify power quality related issues in equipment with power quality indicator (378 FC)



Buy a Fluke 376 FC and receive a FREE:

Fluke T5-1000 Electrical Tester

Valued at \$334.00



Buy a Fluke 377 FC and receive a FREE:

Fluke T6-600 Electrical Tester

Valued at \$374.00



Buy a Fluke 378 FC and receive a FREE:

Fluke T6-1000 Electrical Tester

Valued at \$451.00



Fluke Electrical Testers

Fluke T6 Series Electrical Testers

Measure voltage up to 1000 V AC through the open fork, without making contact with live voltage*, opening covers or removing wire nuts; on cables up to AWG 4/0 (120 mm²), carrying as much as 200 A.

- FieldSense™ technology for making non-contact AC voltage, current and frequency measurements
- Simultaneous voltage and current display (T6-1000 & T6-1000 PRO)
- Visual continuity™ – the screen lights up green when continuity is detected. (T6-1000 PRO)

*Voltage measurement requires capacitive path to ground, provided through the user or test lead.



Buy a Fluke T6-600 and receive a FREE:

Fluke 1AC-II VoltAlert™ Electrical Tester


Valued at \$86.00



Buy a Fluke T6-1000 and receive a FREE:

Fluke C150 Soft Carrying Case

Valued at \$108.00



Buy a Fluke T6-1000 PRO and receive a FREE:

Fluke 1AC-II + TPAK Magnetic Hanger

Valued at \$182.00





Fluke 1660 Series Multifunction Installation Testers

The Fluke 1660 Series Multifunction Installation Testers verify the safety of electrical installations in domestic, commercial and industrial applications. They can ensure that fixed wiring is safe and correctly installed to meet the requirements of all relevant local standards.

- Insulation PreTest: Protect the installation and avoid costly mistakes
- Auto Test: Reduce test time up to 40% - Start a sequence of seven critical tests with one press of the TEST button
- Fluke Connect®: View test results, share and retrieve stored results on your smartphone via the Fluke Connect® mobile app (1664 FC)

	1662 AU	1663 FVF/AU	1664 FC FVF/AU
Covering all basic installation test functions	•	•	•
Test smooth DC sensitive RCDs (Type B/B+)		•	•
Earth resistance		•	•
Fluke FVF-SC2 reporting software included		•	•
Insulation PreTest™ safety functions			•
Insulation at L-N, L-PE, N-PE inputs			•
Auto Test Sequence			•
Fluke Connect® compatibility			•



Buy a Fluke 1662 AU and receive a FREE:

Fluke Insulated Hand Tools Starter Kit

Valued at \$328.00



Buy a Fluke 1663 FVF/AU with FlukeView® Forms Documenting Software and receive a FREE:

Fluke T6-600 Electrical Tester

Valued at \$374.00



Buy a Fluke 1664 FC FVF/AU with FlukeView® Forms Documenting Software and receive a FREE:

Fluke 325 400A AC True-RMS Clamp Meter

Valued at \$402.00





Fluke 11x Series Digital Multimeters

Six dependable Digital Multimeters for home improvement, Electrical and HVAC applications.

- Fluke 117: includes integrated VoltAlert™ non-contact voltage detector and LoZ ghost voltage detector feature to get the job done faster
- Fluke 116: HVAC/R Multimeter with temperature, microamps, and LoZ to quickly troubleshoot problems with HVAC/R equipment
- Fluke 115: compact meter for a wide variety of electrical/electronic testing applications

	110	113	114	115	116/HVAC	117
True RMS Readings	AC	AC	AC	AC	AC	AC
Voltage AC/DC	600 V	600 V	600 V	600 V	600 V	600 V
Current AC/DC	-	-	-	10.0 A	600.0 µA	10.0 A
Temperature	-	-	-	-	+400 °C	-
CAT Rating	CAT III 600 V	CAT IV 600 V	CAT III 600 V	CAT III 600 V	CAT III 600 V	CAT III 600 V
VoltAlert™						•



Buy a Fluke 115 Digital Multimeter and receive a FREE:

Fluke C25 Large Soft Case

Valued at \$90.00



Buy a Fluke 116 or 117 and receive a FREE:

Fluke TPAK ToolPak™ Magnetic Hanger

Valued at \$95.00



Fluke 170 Series Digital Multimeters

For professional technicians worldwide there is one preferred solution: the precision, reliability and ease of use they find in Fluke 170 Series True-RMS Digital Multimeters.

- True RMS voltage and current measurements
- Basic accuracy of 0.15% (175) and 0.09% (177 & 179)
- Analogue bar graph
- Temperature measurements (179)



Buy a Fluke 175 or 177 True-RMS Digital Multimeter and receive a FREE:

Fluke TL220 SureGrip™ Industrial Test Lead Set

Valued at \$180.00




Buy a Fluke 179 True-RMS Digital Multimeter and receive a FREE:

Fluke TLK-225 SureGrip™ Master Accessory Set

Valued at \$308.00





Fluke 1507 and 1587 FC Insulation Testers

Fluke Insulation Resistance Testers provide noise-free, reliable results. With advanced performance, the insulation tester line is designed to be safe, simple to use and gimmick-free. A perfect solution for insulation testing, troubleshooting, commissioning and preventative maintenance applications.



Buy a Fluke 1507 and receive a FREE:

Fluke 323 True-RMS Clamp Meter

Valued at \$290.00



Buy a Fluke 1587 FC and receive a FREE:

Fluke 325 400A AC True-RMS Clamp Meter

Valued at \$403.00



Fluke Thermal Imaging



Fluke PTi120, TiS20+ and TiS20+ MAX Infrared Cameras

- 3.5" touchscreen with IR-Fusion™ blending by just sliding your finger across the screen
- 120 × 90 infrared resolution
- Temperature range of -20°C to 150°C (TiS20+), -20°C to 400°C (PTi120/TiS20+ MAX)



Buy a Fluke PTi120 and receive a FREE:

Fluke Insulated Hand Tools Starter Kit

Valued at \$328.00



Buy a Fluke TiS20+/MAX and receive a FREE:

Fluke Pack30 Backpack + Insulated Hand Tools Starter Kit

Valued at \$637.00



How to redeem your FREE bonus:

- 1 Purchase an eligible Fluke test tool between 1 December 2021 and 28 February 2022.
- 2 Visit ➔ [fluke.co/NYNG22](https://www.fluke.co/NYNG22) to redeem.

Authorised Service Provider

For warranty, repair and calibration, Fluke Australia recommends Plus ES.



PLUS-ES

Sponsored by Fluke Australia Pty Ltd. All prices are Fluke Australia's recommended trade price including GST unless specified otherwise. Final pricing is at the discretion of the participating authorised Fluke Australia distributor or wholesaler. Customers purchasing via a wholesaler branch need to ensure the select branch is purchasing Fluke equipment from a Fluke Australia authorised distributor, a full list of which can be found here: www.fluke.com/au/wtb to be valid to redeem within this promotion. Offers are available to customers only. Distributors and/or branches cannot redeem the free items. All redemptions will be checked and verified by Fluke Australia. Fluke rewards can be redeemed online only at: www.fluke.co/NYNG22 with proof of purchase. Offer is valid for purchases made between 1 December 2021 and 28 February 2022 or until stocks last. Offers cannot be combined with any other discounts, promotions or other special offers. Please allow 6-12 weeks for delivery of redeemed items. Offers available to Australian and New Zealand residents only.